






PRODUCT NUMBER

SEE PART NO. TABLE



NOTES:


1. MATERIAL: NYLON 66, UL94V-0. COLOR: NATURAL.
2. THIS HSG IS USED WITH FCI RECEPTACLE TERMINAL 10127817.
3. THIS RECEPTACLE MATES WITH FCI PLUG 10127816, 10127819 & 10127820.
4. PRODUCT SPECIFICATION: GS-12-1181.
5. PACKAGE SPECIFICATION: GS-14-2362.
6. PART NUMBER SCHEME:
10127815- XX LF

POS. CODE:
02: 2 POS.
04: 4 POS.
S
24: 24 POS.


7. DIMENSIONAL & PART NO. TABLE:

PART NUMBER	PDS.	A	B	C
10127815-02LF	2	/	5.4	3.30
10127815-04LF	4	4.2	9.6	
10127815-06LF	6	8.4	13.8	
10127815-08LF	8	12.6	18.0	
10127815-10LF	10	16.8	22.2	
10127815-12LF	12	21.0	26.4	3.60
10127815-14LF	14	25.2	30.6	
10127815-16LF	16	29.4	34.8	
10127815-18LF	18	33.6	39.0	
10127815-20LF	20	37.8	43.2	
10127815-22LF	22	42.0	47.4	
10127815-24LF	24	46.2	51.6	


mat'l. code		surface	tolerance	projection	product family
ltr	ecn no	dr	date		RECEPTACLE HSG, DUAL ROW, FOR 4.2mm PITCH WIRE CONNECTOR
A		TAI	2013-11-11		
		tolerances unless otherwise specified		MM	title
		angles	X.X ±0.4		
		fillet	X.XX ±0.3	scale	sheet 1 of 2 size
		X°±1°			
		dr	KENNY TAI 2013-11-11		10127815 A4
		enr	KENNY TAI 2013-11-11		
		chr	KENNY TAI 2013-11-11		
		appd	PM ZHENG 2013-11-22		
sheet index	revision sheet	A	A	type CUSTOMER Drawing	
		1	2		




2 POS




10 POS




18 POS




4 POS




12 POS




20 POS




6 POS




14 POS




22 POS



8 POS



16 POS



24 POS

mat'l. code		surface		tolerance		projection		product family	
ltr		ecn no		dr		date		title	
								RECEPTACLE HSG, DUAL ROW, FOR 4.2mm PITCH WIRE CONNECTOR	
				angles		X.X ±0.4		sheet 2 of 2	
				X.XX ±0.3		MM		size	
				X*±1*		scale		A4	
		dr		KENNY TAI		2013-11-11		dwg no	
		enr		KENNY TAI		2013-11-11		10127815	
		chr		KENNY TAI		2013-11-11		type	
		appd		PM ZHENG		2013-11-22		CUSTOMER Drawing	
sheet index		revision sheet		A 1		A 2			

