



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A		增加2P的图、变更2P的尺寸	17.07.10	苏亮



2P 专用


Specifications:
 Current rating: 4A AC/DC.
 Voltage rating: 125V AC/DC
 Temperature range: -40°C~+105°C.
 Contact resistance: 10MΩ Max.
 Insulation resistance: 1000MΩ Min.
 Withstanding voltage: 1000V AC/minute.
 Material: PA66.UL94V-0.



2P 专用

PART NO.	Dimensions		
	A	B	C
A2007WV-02P	2.00	/	5.96
A2007WV-03P	4.00	/	7.95
A2007WV-04P	6.00	4.00	9.96
A2007WV-05P	8.00	6.00	11.96
A2007WV-06P	10.00	8.00	13.96
A2007WV-07P	12.00	10.00	15.96
A2007WV-08P	14.00	12.00	17.96
A2007WV-09P	16.00	14.00	19.96
A2007WV-10P	18.00	16.00	21.96
A2007WV-11P	20.00	18.00	23.96
A2007WV-12P	22.00	20.00	25.96
A2007WV-13P	24.00	22.00	27.96
A2007WV-14P	26.00	24.00	29.96
A2007WV-15P	28.00	26.00	31.96

Recommended P.C.B Layout(Top Side)
 P.C.B Thickness = 1.20mm (Tolerance=±0.05)



CNJM Joint More Precision electronics Co.,Ltd.

DRAW NO.	DATE	P/N NO:	DRAW NAME:
DESIGN: 陈雪峰	2017.06.03	A2007WV-NP	2.0mm pitch 180°wafer
CHECK: 杨 焯			
REVIEW:		REV. A/1	SCALE 1: 1
		UNIT: mm	SHEET: 1 OF 1

DIM	TOL	DIM	TOL
X.	/	X*.	/
X.X	0.25	X.X*	
X.XX	0.15	X.XX*	
X.XXX	0.10	X.XXX*	/