






环保物料

TEL:0769-82001899

Poles	DIM.A	DIM.B
2	2.0	8.0
3	4.0	10.0
4	6.0	12.0
5	8.0	14.0
6	10.0	16.0
7	12.0	18.0
8	14.0	20.0
9	16.0	22.0
10	18.0	24.0
11	20.0	26.0
12	22.0	28.0
13	24.0	30.0
14	26.0	32.0
15	28.0	34.0
16	30.0	36.0



**SPECIFICATIONS**

- 1.Voltage rating: 250V AC, DC
  - 2.Current rating: 2A, AC, DC
  - 3.Withstanding Voltage: 1000V AC/minute
  - 4.Insulation resistance:1000M min
  - 5.Temperature range: -25 ° C-+85 ° C
  - 6.Contact resistance: 20m max
- WAFER  
 Housing Material: PA9T UL 94V0  
 Pin Material: Phosphor Bronze or Brass  
 Contact Area Plating: Plated Tin or Plated Gold  
 Mates with :P2016 series Housing  
 Poles:02-16P  
 Part No.: M2016RS-xxP

Pin位数

P.C.B LAYOUT

TOLERANCE UNLESS OTHERWISE

**TOLERANCE :**  
 .000 :±0.08  
 .00 :±0.13  
 .0 :±0.25

DRAWN CK tan  
 CHKD  
 APPD  
 VIEW

**XFCN** 兴飞连接器有限公司  
 XFCN CONNECTORS CO.,LTD.

PRODUCT NAME 2.00mm Crimp Style Connectors

PART. NO. M2016RS-xxP

SHEET	1/1
DATE	2020. 04. 12
UNITS	mm
SCALE	1:1
DWG. NO.	009

AO VER MODIFICATION

DRAW DATE