

RoHS

SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance:20mΩ Max

Withstand Voltage:1000V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40℃ to +105℃

Contact Material:Brass




Contact Plating:Au Over Ni

Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230℃ for 30-60 seconds
(260℃ for 10 seconds)

Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



Dimension antitheses list

ITEM	PA	PC	L
Standard	6.00	3.00	11.50
Alternate			

OPERATION

DRAW

SCALE

FIT

深圳市连盛精密连接器有限公司

X.X ±0.30

CHECK

UNIT

mm

X.XX ±0.20

SIZE

A4

PART NO.

PH-00579

X.XXX ±0.10

SHEET

1/1

TITLE:

2.54PH H=2.5 1X1P DIP

Angle ±3°

APPROVE

PROJ.

◆

DIM

TOL

A0 2012.03.28 NEW DRAWING

REV DATE MODIFICATION DESCRIPTION CHANGE