



T:1.6 Dimensions of PCB board holes
Tolerance:±0.1(Printed-side view)

额定电压:20V
Rated voltage:20V
额定电流: 4A
Rated Current: 4A
接触电阻: 30MΩ MAX
Contact resistance: 30MΩ MAX
温度范围:5~+35℃
Temp Range:5~+35℃
气压:86kPa~106kPa
Air pressure:86kPa~106kPa
相对湿度:45%~85%
Relative humidity:45%~85%

SCHEMATIC	
Model	DC-062A-4A
Center Pin	Ø1.0mm
	Ø1.3mm
	Ø1.65mm
	Ø2.0mm
	Ø2.35mm
Ø2.5mm	

6	TERMINAL	1	Brass t=0.4	Cu/Ni/Sn
5	SHUNT TERMINAL	1	Brass t=0.4	Cu/Ni/Sn
4	TIP SPRING	1	Phosphor copper t=0.3	Cu/Ni/Sn
3	PIN	1	Brass	Cu/Ni/Sn
2	COVER	1	PBT	UL 94V-0
1	HOUSING	1	PBT	UL 94V-0
LTR	PART NAME	QTY	MATERIAL	REMARK
DSND	SCALE: N/A		MODEL TYPE: DC POWER JACK	
DWN	VIEW:		PART NO.: DC-062A-4A-2.0	
CHKD	UNIT: mm/in		DWG NO.: X-DC-062A-4A-2.0	
APPD	SIZE: A4		WEIGHT	
			SHEET	REVISION
			1/1	A0

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

UNSPECIFIED TOLERANCES



XKB INDUSTRIAL PRECISION CO., LIMITED

广东星坤科技股份有限公司

生效	日期
MARK	DESCRIPTION
REVISIONS	DATE
REVISED	APPROVED

文件工程章

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn