

CAD FILE:

Technical Data

Material:

Contact material: Phosphor bronze

Plating: Gold Flash

Insulator material: Black polyester UL94V-0

Standard: PA6T+30%G.F

Electrical:

Current rating: 1.0Amps/contact max.

Contact resistance: $\leq 20m\Omega$ /contact





Insulation resistance: $\geq 1000M\Omega$ at $V=100V$

Withstanding voltage: 300V AC/minute

Mechanical:

Soldering temperature: +260°C, 4s max

UNSPECIFIED TOLERANCE: ± 0.20



PCB Layout

$$A = 1.27 * \frac{nP}{2} + 0.4 \pm 0.35$$

$$B = 1.27 * \frac{nP}{2} - 1.27 \pm 0.2$$

Pin Number=2~100

APPROVALS		DATE	DEALON 德之隆® ELECTRONICS CO.,LTD		
DRAWN	G.M.Chen	2015/5/22	TITLE:	CONNECTOR	
CHECKED			PART NO.	DW127S-22-XX-43	
APPROVALS			UNIT: mm	SCALE: 1:1	SHEET 1 OF 1
TOLERANCES ARE		ANGLE	DRAWING NO.		PROJ:
30~PL	± 0.30				
10~30	± 0.20				
5~10	± 0.15	$\pm 2'$			
~ 5	± 0.10				

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			