




- NOTE:
- 1.Rating: 24V 25mA DC
  - 2.Contact Resistance: 50mΩ max
  - 3.Dielectric Strength:500V AC/1Minute
  - 4.Operating Force: 1000gf Max
  - 5.Operating Life:2,000 Cycles



Position(位数)	1P	2P	3P	4P	5P	6P	7P	8P	9P	10P	12P	
DIM.A(长度)	2.65	6.54	9.08	11.62	14.16	16.70	19.24	21.78	24.32	26.86	31.94	
DIM.B(长度)	2.54	2.54	5.08	7.62	10.16	12.70	15.24	17.78	20.32	22.86	27.94	
PART NO.	凸柄(P)	SC-02KP	SC-02KP	SC-03KP	SC-04KP	SC-05KP	SC-06KP	SC-07KP	SC-08KP	SC-09KP	SC-10KP	SC-12KP
盖子/黑色(K)	短柄(S)	SC-02KS	SC-02KS	SC-03KS	SC-04KS	SC-05KS	SC-06KS	SC-07KS	SC-08KS	SC-09KS	SC-10KS	SC-12KS

ITEM	PART NAME	QTY.	MATERIAL	FINISHING
④	Terminal		Phosphor bronze	Au Plating
③	Base	1	PBT	Black
②	Cover	1	PBT	Black
①	Keystoke	1	PBT	White

APPROVALS		DATE				
DRAWN	G.M.Chen	2015/6/26				
CHECKED			TITLE:	DIP SWITCHES		
APPROVALS			PART NO.	SC-XXXX		
TOLERANCES ARE		30~以上 ±0.30	ANGLE	UNIT: mm	SCALE: 1:1	SHEET 1 OF 1
		10~30 ±0.20		DRAWING NO.		PROJ:
		5~10 ±0.15	±2'			
		~ 5 ±0.10				

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			