



Recommend PCB Layout

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 工作温度:  $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 适用线规: AWG#30~#22
4. 额定电压: 250V DC/AC(rms)
5. 额定电流: 3.0A
6. 接触电阻:  $\leq 20\text{m}\Omega$
7. 耐压值: 1000V AC/minute
8. 绝缘电阻:  $\geq 1000\text{M}\Omega$ 。

Poles	Dimensions (mm)	
	A	B
1	2.50	7.50
2	2.50	7.50
3	5.00	10.00
4	10.00	12.50
5	10.00	15.00
6	12.50	17.50
7	15.00	20.00
8	17.50	22.50
9	20.00	25.00
10	22.50	27.50
11	25.00	30.00
12	27.50	32.50
13	30.00	35.00
14	32.50	37.50
15	35.00	40.00
16	37.50	42.50

APPROVALS		DATE	TOLERANCES ARE		ANGLE	PART NO.	SCALE:	SHEET
DRAWN	G.M.Chen	2015/7/17	30 <sup>±0.15</sup>	±0.30	ANGLE	XH-W-XXA	1:1	1 OF 1
CHECKED			10 <sup>±0.10</sup>	±0.20	±2°	Connector		
APPROVALS			5 <sup>±0.10</sup>	±0.15				
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.		PROJ.
	A		NEW					

**DEALON** 德之隆  
ELECTRONICS CO.,LTD