



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 工作温度: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 适用线规: AWG#30~#22
4. 额定电压: 250V DC/AC(rms)
5. 额定电流: 3.0A
6. 接触电阻: $\leq 20\text{m}\Omega$
7. 耐压值: 1000V AC/minute
8. 绝缘电阻: $\geq 1000\text{M}\Omega$ 。

Poles	Dimensions (mm)	
	A	B
1	2.50	7.50
2	2.50	7.50
3	5.00	10.00
4	10.00	12.50
5	10.00	15.00
6	12.50	17.50
7	15.00	20.00
8	17.50	22.50
9	20.00	25.00
10	22.50	27.50
11	25.00	30.00
12	27.50	32.50
13	30.00	35.00
14	32.50	37.50
15	35.00	40.00
16	37.50	42.50

APPROVALS		DATE																	
DRAWN	G.M.Chen	2015/7/17																	
CHECKED																			
APPROVALS																			
TITLE: Connector PART NO. XH-W-XXA UNIT: mm SCALE: 1:1 SHEET 1 OF 1 DRAWING NO. PROJ.																			
TOLERANCES ARE: <table border="1" style="display: inline-table; margin-left: 20px;"> <tr> <td>30~40</td> <td>±0.30</td> <td>ANGLE</td> <td></td> </tr> <tr> <td>10~30</td> <td>±0.20</td> <td></td> <td></td> </tr> <tr> <td>5~10</td> <td>±0.15</td> <td></td> <td></td> </tr> <tr> <td>~5</td> <td>±0.10</td> <td></td> <td></td> </tr> </table>				30~40	±0.30	ANGLE		10~30	±0.20			5~10	±0.15			~5	±0.10		
30~40	±0.30	ANGLE																	
10~30	±0.20																		
5~10	±0.15																		
~5	±0.10																		
ECN NO.	REV.	DESCRIPTION.	CHANGE.																
	A	NEW																	

DEALON 德之隆
ELECTRONICS CO.,LTD