




B±0.25



P.C.B LAYOUT

Poles	Dimensions (mm)	
	A	B
1	2.50	7.50
2	5.00	10.00
3	10.00	12.50
4	15.00	15.00
5	20.00	17.50
6	25.00	20.00
7	30.00	22.50
8	35.00	25.00
9	40.00	27.50
10	45.00	30.00
11	50.00	32.50
12	55.00	35.00
13	60.00	37.50
14	65.00	40.00
15	70.00	42.50
16	75.00	45.00



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -25° C~85° C.
3. 额定电压: 50V, AC,DC.
4. 接触电阻: ≤0.02Ω.
5. 绝缘电阻: ≥100MΩ.

APPROVALS		DATE	TOLERANCES ARE		ANGLE	UNIT	SCALE	SHEET
DRAWN	G.M.Chen	2015/7/17	30 ^{±0.15}	±0.30	±2°	mm	1:1	1 OF 1
CHECKED			10 ^{±0.10}	±0.20				
APPROVALS			5 ^{±0.05}	±0.10				
ECN NO.	REV.	DATE.	DESCRIPTION.		CHANGE.	CHECK.	APPRO.	PROJ.
	A		NEW					

DEALON 德之隆
ELECTRONICS CO.,LTD

2.5 Pitch 直插

XHB-D-XXA

SHEET 1 OF 1