



REV.	ECN. NO.	APPD.
A		

NOTES:
 Current Rating: 3.0AMP
 Withstand Voltage: 500V AC/DC
 Contact Resistance: 20mΩ Max
 Insulation Resistance: 1000MΩMin
 Operation Temperature: -40°C to +105°C
 Contact Material: Phosphor Bronze
 Contact plating: Au or Sn over Ni
 Insulator Material: PA6T+30%G. F UL94V-0



Recommended P.C.B Layout(TOP Side)
 (PCB BOARD TOLERANCE±0.05)




Ordering Information

MTF150-2XX M U X

No. of Pins per ROW: 02-40PIN
 Series No.
 1=TYPE 1
 2=TYPE 2



TYPE 2 WITH POST



TYPE 1 W\O POST

X. ± 0.30	X.° ± 5°	UNITS mm	NAME (INTENDED USE)	MINTRON CO.,LTD.
.X ± 0.20	.X° ± 2°	MAT'L	PART NO. (INTENDED USE)	
.XX ± 0.10	.XX° ± 1°	FINISH	APPD: SUNNY	TITLE: FH2.54 DUAL ROW SMT H=5.0
.XXX ± 0.05	.XXX° ± 0.5°		Q'TY	CHKD: LISA
FEMALE HEADER CONNECTOR			DR: ZOE 2006-11-28	SCALE 1/1
				SHEET 1/1
				REV. A