




REV.	ECN. NO.	APPD.
A		

NOTES:  
 Current Rating:3.0AMP  
 Contact Resistance:20mΩ max  
 Withstand Voltage:500V AC/DC  
 Insulation Resistance:1000MΩ mi  
 Operation Temperature:-40°C to +105°C


Contact Material:Phosphor Bronze  
 Contact plating:Au or Sn Over Ni  
 Insulator Material:PBT or PA6 +30%GF(UL94V-0)  
 Contact plated:Gold Flash



Recommended P.C.B Layout(TOP Side)  
 (PCB BOARD TOLERANCE±0.05)



SECTION: B-B



SECTION: A-A

### Ordering Information

MTF150-2XXSU1

No. of Pins per ROW:02-40PIN

X. ± 0.30	X.° ± 5°	UNITS	mm	NAME(INTENDED USE)	MINTRON CO.,LTD.	
.X ± 0.20	.X° ± 2°	MAT'L		PART NO.(INTENDED USE)		
.XX ± 0.10	.XX° ± 1°	FINISH		APPD: SUNNY	TITLE: FEMALE HEADER 2.54 DUAL ROW H=5.0 180°	
.XXX ± 0.05	.XXX° ± 0.5°		Q'TY		CHKD: LISA	DWG NO.: MTF150-2XXSU1
FEMALE HEADER CONNECTOR				DR: ZOE	2006-11-28	
				SCALE	SHEET	REV.
				1/1	1/1	A