

NOTES:

MATERIAL:

Insulator: High Temperature Thermoplastic, UL 94V-0.
 Contact: Copper Alloy
 CD PIN: Copper Alloy
 Shell: STAINLESS


Electrical:


Current Rating :0.5mA AC/DC max.
 Voltage Rating :10V AC/DC
 Ambient Temperature Range :-40°C~+85°C
 Storage Temperature Range :-40°C~+85°C
 Ambient Humidity Range :95% R.H. Max.
 Contact Resistance:100m Ω max.
 Insulation Resistance:1000M Ω min./500VDC
 Mating Cycles:5,000 Insertions
 Temperature:260°C \pm 5°

ELECTRIC FUNCTION	DETECT SWITCH
WITHOUT CARD	OPEN
CARD INSERTED	CLOSED




MANUFACTURE DWG	
UNLESS OTHERWISE SPECIFIED TOLERANCES	
DECIMALS:	ANGLES:
.X: \pm 0.30	X': \pm 2'
.XX: \pm 0.20	X.X': \pm 1'
.XXX: \pm 0.10	


 东莞市讯普电子科技有限公司
 DongGuan XunPu Electronics Co.,Ltd




TITLE: SIM PUSH H2.9 8+1 客户图	
PAR	SIM-133-ACP9
DWN	
CHKD	
APVD	
SCALE1:1	UNIT:MM
SIZE:A4	SHEET:1F1
Website address	REV:A






NOTES

1. 每卷包装数量: 500PCS/每卷
2. 卷带包装方式:



3. 每箱包装数量: 3000PCS/箱



MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	TITLE: SIM PUSH H2.9 8+1 客户图	
UNLESS OTHERWISE SPECIFIED TOLERANCES			PAR	SIM-133-ACP9
DECIMALS:	ANGLES:	DWN		
.X:±0.30	X.'':±2'	CHKD		
.XX:±0.20	X.X':±1"	APVD		
.XXX:±0.10		SCALE1:1	UNIT:MM	
		SIZE:A4	SHEET:1F1	REV:A
		Website address		