







修订 REV	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
AO		NEW RELEASE	黄艳兰	2021-04-12



3D VIEW



PIN数	A±0.1	B±0.1	C±0.1
2P	8.00	4.70	2.00
3P	10.00	6.70	4.00
4P	12.00	8.70	6.00
5P	14.00	10.70	8.00
6P	16.00	12.70	10.00
7P	18.00	14.70	12.00
8P	20.00	16.70	14.00
9P	22.00	18.70	16.00
10P	24.00	20.70	18.00

C	插片	黄铜	镀镍锡	
B	插针	黄铜	镀镍锡	
A	基座	LCP	本色	
序号	品名	材质	电镀/颜色	备注

Specifications:

- 1.Rated Voltage : 250V AC/DC
- 2.Rated Current : 5A AC,DC
- 3.Withstand Voltage : 1000V AC/minute
- 4.Contact Resistance : 50mΩ(MAX.)
- 5.Insulation Resistance : 1000MΩ(MIN.)
- 6.Storage Temperature Range:-40°C~+85°C;
- 7.Operation Temperature Range:-25°C~+70°C;




深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

TEL : 0755-27111225 FAX : 0755-29940187

-TOLERANCES-
UNLESS OTHERWISE SPECIFIED
公差参数表



TITLE:
产品名称: PH2.0针座卧贴

X.X ±0.30 X.X° ±3°

APPD:
核准: 谢亮

PART NO:
产品编号: HDGC2001WR-S-XP

X.XX ±0.30 X.XX° ±2°

CHECK:
校对: 王建业

DATE SCALE UNIT CODE NUMBER

X.XXX ±0.10 X.XXX° ±1°

DRAW:
绘图: 黄艳兰

2021-04-12 1:1 mm A070