



REV.	ECN. NO.	APPD.
A		

NOTES:  
 Current Rating:1.5AMP  
 Contact Resistance:20mΩ max  
 Withstand Voltage:500V AC/DC  
 Insulation Resistance:1000MΩ min  
 Operation Temperature:-40°C to +105°C

Contact Material:Brass  
 Contact plating:Au or Sn Over Ni  
 Insulator Material:PA6T+30%GF(UL94V-0)






Recommended P.C.B Layout(Top Side)  
 (PCB BOARD TOLERANCE±0.05)



**MTB11-XXR**

No. of Pins	
6P	24P
8P	26P
10P	30P
12P	34P
14P	40P
16P	50P
18P	60P
20P	64P



X. ± 0.30	X.° ± 5°	UNITS mm	NAME(INTENDED USE)	MINTRON CO.,LTD.
.X ± 0.20	.X° ± 2°	MAT'L	PART NO.(INTENDED USE)	
.XX ± 0.10	.XX° ± 1°	FINISH	APPD: SUNNY	TITLE: MTB11-XXR
.XXX ± 0.05	.XXX° ± 0.5°		CHKD: LISA	DWG NO.:
BOX HEADER CONNECTOR		Q'TY	DR: ZOE 2006-11-28	
			SCALE 1/1	