



| | | |
|------|----------|-------|
| REV. | ECN. NO. | APPD. |
| A | | |

NOTES:
 Current Rating:1.5AMP
 Contact Resistance:20mΩ max
 Withstand Voltage:500V AC/DC
 Insulation Resistance:1000MΩ min
 Operation Temperature:-40°C to +105°C

Contact Material:Brass
 Contact plating:Au or Sn Over Ni
 Insulator Material:PA6T+30%GF(UL94V-0)





Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



MTB11-XXR

| | |
|-------------|-----|
| No. of Pins | |
| 6P | 24P |
| 8P | 26P |
| 10P | 30P |
| 12P | 34P |
| 14P | 40P |
| 16P | 50P |
| 18P | 60P |
| 20P | 64P |



| | | | | |
|----------------------|--------------|----------|------------------------|------------------|
| X. ± 0.30 | X.° ± 5° | UNITS mm | NAME(INTENDED USE) | MINTRON CO.,LTD. |
| .X ± 0.20 | .X° ± 2° | MAT'L | PART NO.(INTENDED USE) | |
| .XX ± 0.10 | .XX° ± 1° | FINISH | APPD: SUNNY | TITLE: MTB11-XXR |
| .XXX ± 0.05 | .XXX° ± 0.5° | Q'TY | CHKD: LISA | DWG NO.: |
| BOX HEADER CONNECTOR | | | DR: ZOE | |
| | | | 2006-11-28 | |
| | | | SHEET 1/1 | REV. A |