





REV.	ECN. NO.	APPD.
A		

NOTES:
 Current Rating: 3.0AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 1000V AC/DC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40°C to +105°C

Contact Material: Phosphor Bronze
 Contact plating: Au Or Sn over Ni
 Insulator Material: PA6T+30%G.F UL94V-0
 Contact plated: Gold Flash

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE ±0.05)




Ordering Information

MTF171-2XXSU1

No. of Pins per ROW: 02-40PIN

X. ± 0.30	X.° ± 5°	UNITS	mm	NAME (INTENDED USE)	MINTRON CO.,LTD.
.X ± 0.20	.X° ± 2°	MAT'L		PART NO. (INTENDED USE)	
.XX ± 0.10	.XX° ± 1°	FINISH		APPD: SUNNY	DWG NO.: MTF171-2XXSU1
.XXX ± 0.05	.XXX° ± 0.5°	Q'TY		CHKD: LISA	
FEMALE HEADER CONNECTOR				DR: ZOE	2006-11-28



SCALE	SHEET	REV.
1/1	1/1	A