





REV.	ECN. NO.	APPD.
A		

NOTES:  
 Current Rating: 1.0AMP  
 Withstand Voltage: 500V AC/DC  
 Contact Resistance: 20mΩ Max  
 Insulation Resistance: 1000MΩMin  
 Operation Temperature: -40°C to +105°C

Contact Material: Phosphor Bronze  
 Contact plating: Au or Sn over Ni  
 Insulator Material: PA6T+30%G, F UL94V-0

Recommended P.C.B Layout(Top Side)  
 (PCB BOARD TOLERANCE±0.05)



SECTION A-A

SECTION B-B

## Ordering Information

MTF334-2XXSU1

No. of Pins per  
ROW: 02-40PIN

X. ± 0.30	X.° ± 5°	UNITS	mm	NAME (INTENDED USE)	MINTRON CO.,LTD.				
.X ± 0.20	.X° ± 2°	MAT'L		PART NO. (INTENDED USE)					
.XX ± 0.10	.XX° ± 1°	FINISH		APPD: SUNNY	TITLE: FEMALE HEADER 1.27 DUAL H=3.4 180°				
.XXX ± 0.05	.XXX° ± 0.5°		Q'TY		CHKD: LISA	DWG NO.: MTF334-2XXSU1			
FEMALE HEADER CONNECTOR				DR: ZOE	2006-11-28		SCALE 1/1	SHEET 1/1	REV. A