

PMP

3.2Ø x 7.1 mm

Time-Lag Fuse



Agency Approvals

Agency	Ampere Rating
Recognized Component for Canada and US	375mA - 7A
PSE	1A - 5A (125V)

Electrical Characteristics

Ampere Rating	Opening Time							
	1 In		2 In		3 In		8 In	
	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX
375mA - 7A	4 hr	1 sec	60 sec	200 ms	3 sec	20 ms	100 ms	

Interrupting Rating

50 amperes at 250V AC/ 125V DC

Product Characteristics

Operating Temperature	-55 °C to 125 °C
Material	Body: Encapsulated, Epoxy-Coated Leads Wire: Tin Plated Copper
Leads Wire	Diameter Ø0.64mm

Catalog Number	Ampere Rating (A)	Voltage Rating (V)	Nominal Cold Resistance (Ohms)	Nominal Melting I ² t (A ² sec.)
PMP .375	375mA	250V	0.3618	0.225
PMP .500	500mA		0.2455	0.484
PMP .600	600mA		0.2442	0.685
PMP .750	750mA		0.1733	1.311
PMP 001	1A		0.1109	2.304
PMP 1.50	1.5A		0.0898	5.103
PMP 002	2A		0.0457	8.748
PMP 2.50	2.5A		0.0313	12.36
PMP 003	3A		0.0242	13.37
PMP 3.50	3.5A		0.0211	19.74
PMP 004	4A		0.0158	22.18
PMP 005	5A		0.0128	45.90
PMP 007	7A		0.0090	91.26

Packaging

Packaging Option	Quantity
In Bulk	2,000 pcs / box

Mechanical Dimensions (mm)

