






P	LTR	DESCRIPTION	DATE	DWN	APVD
	K2	REVISED	14OCT2016	KF	HY



SELECTIVE-TIN (MATTE)	SELECTIVE TIN (BRIGHT) × 14 SELECTIVE GOLD × 2	3, 4	BLACK	2-5175615-2
	PRE-TIN × 14	8, 16	BLACK	3-175615-2
TIN-LEAD	SELECTIVE GOLD × 2			
SELECTIVE-TIN (MATTE)	SELECTIVE-TIN (BRIGHT)	-	BLACK	175615-3
	PRE-TIN	-	BLACK	175615-2
	PRE-TIN	-	WHITE	175615-1
SOLDERING SIDE 半田付け部	CONTACT SIDE 接触部側	GOLD PLATED CIRCUIT NO △ 金めっき回路番号	COLOR 色	PART NUMBER 製品型番
CONTACT FINISH コンタクト仕上				

- THE MATING PLUG HSG. PART NUMBER ; 174909, 175966
 - RECOMMENDED MOUNTING SCREW 3mmDIA
6mmLENGTH (MAX) PAN HEAD, CLASS
2 TAPPING SCREW SPECIFIED IN JIS
B1115, B1122 (TIGHTENING TORQUE ; 39.2N-cm MAX)
- △ 回路番号 (SEE ABOVE)

- 嵌合相手ハウジング ; 174909, 175966
 - 推奨取付ネジ ; JIS B1115, B1122 タッピングネジ、M3X6
ナベ2種 (締付トルク ; 39.2N-cm 以下)
- △ 回路番号 ; 上図参照のこと

GENERAL TOLERANCE

0<*i 10	: ±0.2
10<*i 30	: ±0.25
30<*i 100	: ±0.3
角 度	: ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 単位: 耗 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差	DWN M.KADOSAKI 13OCT05	TE Connectivity
	0 PLC ±-	CHK T.SHINOHARA 13OCT05	
	1 PLC ±-	APVD K.BETSUI 13OCT05	
	2 PLC ±-	NAME 名称	
	3 PLC ±-	PRODUCT SPEC 製品規格	16POS CAP HOUSING ASSY 040 SERIES MULTI-LOCK I/O CONNECTOR MK-II
	4 PLC ±-	APPLICATION SPEC 取付適用規格	SIZE A3
	ANGLES ±-	WEIGHT 5.8 g	CAGE CODE 00779
MATERIAL 材料 PBT : HOUSING BRASS : TAB	FINISH 仕上 COLOR : SEE TABLE	CUSTOMER DRAWING	DRAWING NO 番号 C-175615
		SCALE 尺度 2:1	RESTRICTED TO —
		SHEET 1 OF 1	REV K2