




# RoHS

CAD GENERATED DRAWING. DON'T CHANGE BY HAND.

REV.	ECN. NO.	APPD.



### Specification

Operating Life	300,000
Contact rating	50mA@12V DC.
Insulation resistance	1011Ω min.
Contact resistance	100mΩ max.initial.
Dielectric Strength	250 V AC(1mm)
Travel	0.15±0.1mm
Storage Temperature	-30° C to 85° C

E	STEM	PART	1	Black
D	COVER	Stainless Steel	1	AU
C	DOME	Stainless Steel	1	Plated Ag
B	HOUSING	LCP	1	White
A	PIN	PHOSPHOR BRONZE	1	Plated Ag
ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR

### Mechanical

PN	Operating Force (gf)	Height mm
YTS1T0342AJ00	220±50	2.6
YTS1T0341AJ00	160±50	2.6

Packaging:  
Reel of 3,000 pieces.

X. ±0.50	X.° ±2°	UNITS mm		深圳市怡远科技有限公司 SHENZHEN YIYUAN TECHNOLOGY CO., LTD		
.X ±0.30	.X° ±1°			PART NO. YTS1T034	TITLE: TACTILE SWITCH	
.XX ±0.10	.XX° ±0.5°	MAT'L	APPD: ROGER	DWG NO.: YTS1T034		
.XXX ±0.05		FINISH	CHKD: ROC			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD			DR: BILLY WANG 2020/08/21			
			Q'TY	SCALE	SHEET	REV.
				1/1	1/1	A1