







RoHS

CAD GENERATED DRAWING. DON'T CHANGE BY HAND.

REV.	ECN. NO.	APPD.



SCHEMATIC



P.C.B.LAYOUT

* CRITICAL DIMENSION

- ELECTRICAL CHARACTERISTICS**
1. RATING: DC 30V 0.1A
 2. CONTACT RESISTANCE: 100mΩ MAX
 3. INSULATION RESISTANCE: 100MΩ MIN
 4. DIELECTRIC STRENGTH: AC 250V (50~60Hz)/60S
- MECHANICAL CHARACTERISTICS**
1. PRACTICAL TEMPERATURE RANG: -40°C~+85°C
 2. OPERATING FORCE: 140±50gf
 3. MECHANICAL LIFE: 20,000 cycles

NO.	PART NAME	Q' TY	MATERIAL	FINSH/COLOR
7	CAM STICK	1	SUS	NATURAL
6	TERMINAL	6	BRASS STRIP	Ag COATING
5	CASE	1	PA66	GRAY
4	CONTACT	2	BRONZE	Ag CLAD
3	COVER	1	PPA	BLACK
2	SPRING	1	SUS	NATURAL
1	KNOB	1	POM	BLUE

X. ±0.50	X.° ±2°	UNITS mm
.X ±0.30	.X° ±1°	
.XX ±0.10	.XX° ±0.5°	MAT'L
.XXX ±0.05		FINISH
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD		Q' TY

yiYUAN 深圳市怡远科技有限公司
SHENZHEN YIYUAN TECHNOLOGY CO., LTD

PART NO. YTS70L140DU4	TITLE: 按钮开关7.0*7.0 自锁插脚 3.9*3.9 平头 4脚
APPD: ROGER	DWG NO.: YTS70L140DU4
CHKD: ROC	SCALE SHEET REV. 1/1 1/1 A1
DR: BILLY WANG 2020/08/21	