


Recommended Card Layout



Recommended Card Layout

E=2.54mm FEMALE EDGE SLOT
 D=DIP STRAIGHT 180°
 NO. OF PINS:04-128
 B=Brass + PBT
 P=Phosphor Bronze + PBT

Order Information

E D xxx B GF BK

BK=Black
 GN=Green
 BU=Blue
 GF=1u" Glod Flash
 03=3u" Glod
 05=5u" Glod
 10=10 u" Glod
 15=15 u" Glod
 A3=3u" All Glod

SPECIFICATION

Current Rating:3A
 Dielectric Withstanding Voltage:1000V AC/Minute
 Contact Resistance:20 Milliohms Max
 Insulation Resistance:5000 Megaohms Min. At 500V DC
 Operation Temperature:-55°C~+125°C
 Insertion Force:0.4Kgf Max. Per Pair
 Withdrawal Force:0.25Kgf Max. Per Pair

Insulator:PBT+G.F. (UL94V-0)
 Contact:Brass or Phosphor Bronze
 Gold Plated On Contact Area
 Tin Plated On Solder Tails, Over Nickel

RoHS Compliant

Pin	A	B	C	D	Pin	A	B	C	D
4	2.54	7.92	11.37	9.62	64	78.74	84.12	87.57	85.82
6	5.08	10.46	13.91	12.16	66	81.28	86.66	90.11	88.36
8	7.62	13	16.45	14.7	68	83.82	89.2	92.65	90.9
10	10.16	15.54	18.99	17.24	70	86.36	91.74	95.19	93.44
12	12.7	18.08	21.53	19.78	72	88.9	94.28	97.73	95.98
14	15.24	20.62	24.07	22.32	74	91.44	96.82	100.27	98.52
16	17.78	23.16	26.61	24.86	76	93.98	99.36	102.81	101.06
18	20.32	25.7	29.15	27.4	78	96.52	101.9	105.35	103.6
20	22.86	28.24	31.69	29.94	80	99.06	104.44	107.89	106.14
22	25.4	30.78	34.23	32.48	82	101.6	106.98	110.43	108.68
24	27.94	33.32	36.77	35.02	84	104.14	109.52	112.97	111.22
26	30.48	35.86	39.31	37.56	86	106.68	112.06	115.51	113.76
28	33.02	38.4	41.85	40.1	88	109.22	114.6	118.05	116.3
30	35.56	40.94	44.39	42.64	90	111.76	117.14	120.59	118.84
32	38.1	43.48	46.93	45.18	92	114.3	119.68	123.13	121.38
34	40.64	46.02	49.47	47.72	94	116.84	122.22	125.67	123.92
36	43.18	48.56	52.01	50.26	96	119.38	124.76	128.21	126.46
38	45.72	51.1	54.55	52.8	98	121.92	127.3	130.75	129
40	48.26	53.64	57.09	55.34	100	124.46	129.84	133.29	131.54
42	50.8	56.18	59.63	57.88	102	127	132.38	135.83	134.08
44	53.34	58.72	62.17	60.42	104	129.54	134.92	138.37	136.62
46	55.88	61.26	64.71	62.96	106	132.08	137.46	140.91	139.16
48	58.42	63.8	67.25	65.5	108	134.62	140	143.45	141.7
50	60.96	66.34	69.79	68.04	110	137.16	142.54	145.99	144.24
52	63.5	68.88	72.33	70.58	112	139.7	145.08	148.53	146.78
54	66.04	71.42	74.87	73.12	114	142.24	147.62	151.07	149.32
56	68.58	73.96	77.41	75.66	116	144.78	150.16	153.61	151.86
58	71.12	76.5	79.95	78.2	118	147.32	152.7	156.15	154.4
60	73.66	79.04	82.49	80.74	120	149.86	155.24	158.69	156.94
62	76.2	81.58	85.03	83.28	128	160.02	165.4	168.85	167.1



深圳市格林柏电子技术开发有限公司

X. ± 0.30	APPD:	PART NO: EDxxxBGFBK
.X ± 0.20	CHKD:	
.XX ± 0.10	CHKD: HZF	
.XXX ± 0.05	DR:	DWG NO:
X° ± 1°	DR:	
.X° ± 0.5°	UNITS: mm	SCALE: 1:1
	UNITS: mm	SCALE: 1:1
REV	ECN NO	DESCRIPTION
DATE		

REV	ECN NO	DESCRIPTION	DATE