



PCB LAYOUT



Material  
 Insulator: Glass filled PBT, (UL 94V-0)  
 Contact : Brass

Electrical Characteristics  
 Current rating: 2AMP  
 Dielectric Withstanding Voltage: AC 500V for 1 Minute.  
 Insulator Resistance: 1000MΩ Min. AT DC 500V.  
 Contact Resistance: 20mΩ Max.  
 Operating Temperature: -45°C ~ +105°C

PIN \ 尺寸	A±0.15	B±0.2	C±0.2	D±0.1
DR-9M	17.90	25.00	30.80	12.50
DR-15M	26.50	33.30	39.20	12.50
DR-25M	40.00	47.10	53.05	12.50
DR-37M	56.50	63.50	69.44	12.50

			D-SUB-DR-*M		上海洲日电子有限公司 Shanghai Zhouri Electronics CO.,LTD		
X.	±0.3	±5°			上海康司玛电子设备进出口有限公司		
X.X	±0.2	±3°			Shanghai KangSiMa Eletronic Equipment import and export Co.,LTD		
X.XX	±0.15				TEL:86-21-34975176/51571121		
			201171018	物料编号	201171018	1:1	mm 图幅 A4
			201171018				
			201171018				



: 1 1