








| REV. | ECN NO. | DESCRIPTION | DATE | DESIGN |
|------|---------|-------------|------|--------|
|      |         |             |      |        |



Specifications:  
 Current rating:3A AC/DC.  
 Voltage rating:250V AC/DC  
 Temperature range:-25°C~+85°C.  
 Contact resistance:10MΩ Max.  
 Insulation resistance:1000MΩ Min.  
 Withstanding voltage: 800V AC/minute.  
 Material:PA6T.UL94V-0.

| PART NO.      | Dimensions |       |       |
|---------------|------------|-------|-------|
|               | A          | B     | C     |
| A2012WV-S-02P | 2.00       | 8.00  | 4.50  |
| A2012WV-S-03P | 4.00       | 10.00 | 6.50  |
| A2012WV-S-04P | 6.00       | 12.00 | 8.50  |
| A2012WV-S-05P | 8.00       | 14.00 | 10.50 |
| A2012WV-S-06P | 10.00      | 16.00 | 12.50 |
| A2012WV-S-07P | 12.00      | 18.00 | 14.50 |
| A2012WV-S-08P | 14.00      | 20.00 | 16.50 |
| A2012WV-S-09P | 16.00      | 22.00 | 18.50 |
| A2012WV-S-10P | 18.00      | 24.00 | 20.50 |
| A2012WV-S-11P | 20.00      | 26.00 | 22.50 |
| A2012WV-S-12P | 22.00      | 28.00 | 24.50 |
| A2012WV-S-13P | 24.00      | 30.00 | 26.50 |
| A2012WV-S-14P | 26.00      | 32.00 | 28.50 |
| A2012WV-S-15P | 28.00      | 34.00 | 30.50 |



PCB LAYOUT

| DIM   | TOL  | DIM    | TOL |
|-------|------|--------|-----|
| X.    | /    | X*     | /   |
| X.X   | 0.25 | X.X*   | /   |
| X.XX  | 0.15 | X.XX*  | /   |
| X.XXX | 0.10 | X.XXX* | /   |

**CNJM** Joint More Precision electronics Co.,Ltd.

| DRAW NO.    | DATE       | P/N NO.      | DRAW NAME:             |
|-------------|------------|--------------|------------------------|
| DESIGN: 陈雪峰 | 2018.03.29 | A2012WV-S-NP | 2.0mm pitch 180° wafer |
| CHECK: 杨焯   |            |              |                        |
| REVIEW:     |            | REV.A/2      | SCALE 1:1              |
|             |            | UNIT: mm     | SHEET: 1 OF 1          |