



| REV | ECN NO. | DESCRIPTION | DATE | DESIGN |
|-----|---------|-------------|------|--------|
| A | | | | |

NOTES:

CURRENT RATING:3A AC/DC.
 VOLTAGE RATING:250V AC/DC
 TEMPERATURE RANGE:-40°C~+105°C.
 CONTACT RESISTANCE:30m Ω Max.
 INSULATION RESISTANCE:1000MΩ Min.
 WITHSTANDING VOLTAGE: 1000V AC/MINUTE.
 MATERIAL:PA46.



| PART NO. | Dimensions | |
|---------------|------------|-------|
| | A | B |
| A2100WV-2X04P | 6.00 | 10.00 |
| A2100WV-2X05P | 8.00 | 12.00 |
| A2100WV-2X06P | 10.00 | 14.00 |
| A2100WV-2X07P | 12.00 | 16.00 |
| A2100WV-2X08P | 14.00 | 18.00 |
| A2100WV-2X09P | 16.00 | 20.00 |
| A2100WV-2X10P | 18.00 | 22.00 |
| A2100WV-2X11P | 20.00 | 24.00 |
| A2100WV-2X12P | 22.00 | 26.00 |
| A2100WV-2X13P | 24.00 | 28.00 |
| A2100WV-2X14P | 26.00 | 30.00 |
| A2100WV-2X15P | 28.00 | 32.00 |
| A2100WV-2X16P | 30.00 | 34.00 |
| A2100WV-2X17P | 32.00 | 36.00 |
| A2100WV-2X18P | 34.00 | 38.00 |
| A2100WV-2X19P | 36.00 | 40.00 |
| A2100WV-2X20P | 38.00 | 42.00 |
| A2100WV-2X21P | 40.00 | 44.00 |
| A2100WV-2X22P | 42.00 | 46.00 |

CNJM Joint More Precision electronics Co.,Ltd.

| | | | |
|----------|------|------------|----------------------|
| DRAW NO. | DATE | P/N NO: | DRAW NAME: |
| DESIGN: | 陈雪峰 | 2017.06.03 | A2100WV-2XNP |
| CHECK: | 杨 焯 | | PHB2.0mm pitch wafer |
| REVIEW: | | REV.A/1 | SCALE 1:1 |
| | | UNIT: mm | SHEET: 1 OF 1 |

| DIM | TOL | DIM | TOL |
|-------|------|--------|-----|
| X. | / | X° | / |
| X.X | 0.25 | X.X° | / |
| X.XX | 0.15 | X.XX° | / |
| X.XXX | 0.10 | X.XXX° | / |