

性能

额定电压: 300V-320V

额定电流: 20A

耐电压: AC2000V/1Min

导线线径: 22-12AWG (2.5MM)

温度范围: -40℃至+105℃

最大锁紧扭力: 8kg.cm

材质及电镀


间距: 8.5mm

极数: 2P-4P

螺丝: M3、钢、镀锡

端子: 黄铜、镀锡

塑件: PA66. UL94V-0



UNLESS OTHERWISE SPECIFIED			PLPK8500-NP		上海洲日电子有限公司 Shanghai zhouri Electronics CO.,LTD.					
DIMENSION	TOLERANCE									
	DECIMAL	ANGLE	MODEL NO.	Pin Header	MATERIAL		FINISH			
X.	±0.3	±1°	DWG. NO.	ZR-Pin Header-03	COLOR		QUANTITY			
X.X	±0.2	±0.5°								
X.XX	±0.1									
X.XXX	±0.05									
DESIGNED										
CHECKED			REV.	A	SCALE	1:1	UNIT	mm	SIZE	A4
APPROVED			THE THIRD ANGLE PROJECTION					SHEET OF		PAGES