

4 3 2 1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
C9		REVISED PER ECR-22-149019	16AUG2022	N.H	L.C

PIN POSITION No.1  
 8.5 (6.8)  
 TE  
 (1.95) TRADE MARK (1.95)  
 3.96 (PITCH)  
 C  
 A  
 B  
 (0.7)  
 PIN  
 HOUSING  
 1  
 $\phi 1.60^{+0.1}_{-0.0}$  (PUNCHED HOLE)  
 $\phi 1.65^{+0.1}_{-0.0}$  (DRILLED HOLE)  
 3.96±0.05 (PITCH)

4 2 FIG. 1

- 1 MATING CONN P/N: □-1123722-□
- 2 APPLICABLE P.C.B LAYOUT: SEE FIG. 1
- 3 APPLICABLE P.C.B THICKNESS: 1.60.
- 4 SKETCHES SHOW NO PIN MISSING.
- 5 COMPLY WITH GLOW WIRE REQUIREMENTS FOR PARTS OF NON-METALIC MATERIAL SUPPORTING A CURRENT CARRYING CONNECTION DETAILED IN IEC 60335-1 SECTION 30. (GWT [GLOW WIRE TEST]) 750° SPEC.
- 6 CONTACT: POST TIN OVER BRASS
- 7 HOUSING: PBT, 30% GLASS, UL94-V0(ONLY NATURAL COLOR).
- 8 BALANCE OF X-1123724-X WILL BE REMOVED FROM DRAWING 1123723 IN THE NEAR FUTURE AND ADDED TO THIS DRAWING.
- 9 0 : WITH PIN,  
X : WITHOUT PIN.
- 10 HOUSING: NYLON, 15% GLASS

NO	YES	YES	NO	YES	YES	PIN POSITION											"c"	"B"	"A"	COLOR	POSN	ASS'Y P/N
						27.72	29.12	31.62	NATURAL	8	1-1123724-7											
									NATURAL	11	8-1123724-6											
						39.60	41.00	43.50	NATURAL		7-1123724-6											
									NATURAL		1-1123724-6											
									NATURAL		9-1123724-6											
									NATURAL		7-1123724-5											
									GREEN		6-1123724-5											
									BLACK		5-1123724-5											
						31.68	33.08	35.58	RED	9	4-1123724-5											
									BLUE		3-1123724-5											
									YELLOW		2-1123724-5											
									NATURAL		1-1123724-5											
									ORANGE		9-1123724-4											
									PINK		8-1123724-4											
									GRAY		7-1123724-4											
									NATURAL		7-1123724-1											
									GREEN	7	6-1123724-4											
						23.76	25.16	27.66	BLACK		5-1123724-4											
									RED		4-1123724-4											
									BLUE		3-1123724-4											
									YELLOW		2-1123724-4											
									NATURAL		1-1123724-4											
									NATURAL		7-1123724-3											
									GREEN		6-1123724-3											
									BLACK		5-1123724-3											
						15.84	17.24	19.74	RED	5	4-1123724-3											
									BLUE		3-1123724-3											
									YELLOW		2-1123724-3											
									NATURAL		1-1123724-3											
									GREEN		6-1123724-2											
									BLACK		5-1123724-2											
						7.92	9.32	11.82	RED	3	4-1123724-2											
									BLUE		3-1123724-2											
									YELLOW		2-1123724-2											
									NATURAL		1-1123724-2											
GWT	HOUSING MATERIAL	1	2	3	4	5	6	7	8	9	10	11	"c"	"B"	"A"	COLOR	POSN	ASS'Y P/N				

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN: 18JAN2014 NAGALAKSHMI K  
 CHK: 18JAN2014 MICHELUTTI THOMAS  
 APVD: 18JAN2014 MICHELUTTI THOMAS

PRODUCT SPEC: 108-5609  
 APPLICATION SPEC: 114-32134

TE Connectivity  
 3.96MM PITCH ECONOMY POWER (EP) CONNECTOR HEADER ASSEMBLY

SIZE: A2 CAGE CODE: 00779 DRAWING NO: C=1123724 RESTRICTED TO: -

WEIGHT: - SCALE: N/A SHEET: 1 OF 1 REV: C9

CUSTOMER DRAWING

1471-9 (1/15)