




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J	-	F1	REVISED	ECR-14-017602	25NOV2014	TS	KB



- ① -A- 面より2mmの範囲で測定。
- ② 相手ハウジングと所定の機能を満たして嵌合できること。
- 3. 適用リセプタクルコンタクト型番：170177, 170286, 170307
- 4. 適用製品規格番号：108-5093, 108-5099
- 5. 相手ハウジングとの嵌合力は29.4N (3Kg) 以下、
但し、コンタクトは含まない。

- ① TO BE MEASURED WITHIN 2mm FROM -A-
- ② IN COUPLING WITH THE PLUG HOUSING MATING SATISFIES FUNCTION.
- 3. APPLIDE CONTACTPART NUMBER: 170177, 170286 170307
- 4. PRODUCT SPECIFICATION NUMBER: 108-5093, 108-5099
- 5. IN COUPLING WITH THE PLUG HOUSING MATING FORCE 29.4N (3Kg) MAX. WITHOUT REC CONTACTS.



OBSOLETE	黄 / YELLOW	172024-7
OBSOLETE	灰 / GRAY	172024-6
OBSOLETE	青 / BLUE	172024-5
	緑 / GREEN	172024-4
OBSOLETE	茶 / BROWN	172024-3
	黒 / BLACK	172024-2
	自然色 / NATURAL	172024-1
	色 / COLOR	型番 / PART NUMBER

GENERAL TOLERANCE	
10 ≥	: ±0.2
30 ≥ > 10	: ±0.25
100 ≥ > 30	: ±0.3
ANGLE : ±3°	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.SHINOHARA 30JUL09		CHK K.BETSUI 30JUL09		APVD K.BETSUI 30JUL09		NAME	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		APPLICATION SPEC		MULTI-INTERLOCK CONNECTOR 11 POSITION PLUG HOUSING	
MATERIAL 66 NYLON		FINISH -		SEE NOTE 4		-		RESTRICTED TO -	
				WEIGHT -		SIZE A3		CAGE CODE 00779	
				CUSTOMER DRAWING		DRAWING NO C=172024		SCALE 2:1	
						SHEET 1 of 1		REV F1	