


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT 2003 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
J	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
		02	REVISED	ECR-06-026280	08NOV06	TS	KB



△部分金めっき
 2. 圧着規格 114-5133

△SELECTIVE GOLD
 2. CRIMP SPEC. 114-5133

△SELECTIVE GOLD 部分金めっき	175094-2
PRE-TINNED 錫めっき済	175094-1
FINISH 仕上げ	PN 型番

WIRE RANGE 0.3~0.56mm ² (AWG#22-#20)	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A.YAMAGUCHI 09JUL03	Tyco Electronics AMP K.K. Kawasaki, Japan												
INSULATION DIA. 1.0-1.4 mmφ	DIMENSIONS: 単位: 耗 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差	CHK K.BETSUI 09JUL03													
TOLERANCE UNLESS OTHERWISE SPECIFIED: 一般公差		<table border="1"> <tr><td>0 PLC</td><td>±</td></tr> <tr><td>1 PLC</td><td>±</td></tr> <tr><td>2 PLC</td><td>±</td></tr> <tr><td>3 PLC</td><td>±</td></tr> <tr><td>4 PLC</td><td>±</td></tr> <tr><td>ANGLES</td><td>±</td></tr> </table>	0 PLC	±	1 PLC	±	2 PLC	±	3 PLC	±	4 PLC	±	ANGLES	±	APVD K.BETSUI 09JUL03	NAME 名称 040 SERIES RECEPTACLE CONTACT
0 PLC			±													
1 PLC	±															
2 PLC	±															
3 PLC	±															
4 PLC	±															
ANGLES	±															
0 < x ≤ 10 : ±0.2 10 < x ≤ 30 : ±0.25 30 < x ≤ 100 : ±0.3 ANGLE ; ±3°	MATERIAL 材料 KLE-5 THICKNESS; 0.25	FINISH 仕上 SEE TABLE	PRODUCT SPEC 製品規格 APPLICATION SPEC 取付適用規格 SEE NOTE	SIZE A3												
			WEIGHT -	CAGE CODE 00779												
			CUSTOMER DRAWING	DRAWING NO C-175094												
				RESTRICTED TO -												
				SCALE 尺度 5:1												
				SHEET 1 OF 1												
				REV 02												