




NUMBER C-172076



断面 "A"- "A"
(SECT "A"- "A")



NOTES;

- PRODUCT SPECIFICATION 108-5127
- APPLICABLE CONTACT
P/N ; 170327, 170328, 170329
- SEE CP78-26023. ABOUT APPLICABLE TAB.
- MATERIAL ; 6/6 NYLON (94V-0)
- THERE ARE A FEW CASES THAT SHRINK MARK AND/OR UNTHROUGH HOLE OCCURS IN THIS AREA, BUT NOT INFLUENCE TO CONN, FUNCTION.
- COMPLY WITH GLOW WIRE REQUIREMENT FOR PARTS OF NON-METALLIC MATERIAL SUPPORTING A CURRENT CARRYING CONNECTION DETAILED IN IEC 60335-1, SECTION 30 (GWT), (GWT, UL94V-0)
- MATERIAL: PA66, UL94 V-0, GWIT 775°C

| | | | |
|----------|-----------------------|---------------|----------|
| | 3-172076-1 | NATURAL | |
| OBSOLETE | 7-172076-4 | NATURAL | |
| | 2-172076-7 | (RED) 赤 | |
| | 2-172076-6 | (BLUE) 青 | |
| OBSOLETE | 2-172076-5 | (GREEN) 緑 | |
| | 2-172076-4 | (YELLOW) 黄 | |
| | 2-172076-2 | (BLACK) 黒 | |
| | 2-172076-1 | (NATURAL) 自然色 | |
| | 172076-7 | (RED) 赤 | |
| | 172076-6 | (BLUE) 青 | |
| | 172076-5 | (GREEN) 緑 | |
| | 172076-4 | (YELLOW) 黄 | |
| | 172076-2 | (BLACK) 黒 | |
| | 172076-1 | (NATURAL) 自然色 | |
| | 型番 (P/N) | 色 (COLOR) | 注 (NOTE) |

単位: mm DIMENSIONS IN MM. DO NOT SCALE PRINT

PRINT DIST

| | | | | |
|-----|---------------------------|----------|-----|------|
| H7 | REVISED PER ECR-19-018127 | 20JUL'20 | AA | EW |
| H6 | REVISED PER ECR-19-002938 | 25FEB'19 | BH | E.W |
| REV | DESCRIPTION | DATE | DWN | APVD |

| | | |
|---|-----------------------------------|--|
| TE Connectivity | | |
| 規格電線断面積 (WIRE RANGE) --- mm ² (AWG -) | 被覆外径 (INSULATION DIA.) --- mmφ | 名称 (NAME) 250 シリーズ 1極 ポジティブロック (マークII)ハウジング 250 SERIES 1 Pos POSITIVE LOCK (MK-II) HOUSING |
| 材料 (MATERIAL) 6/6ナイロン (94V-2) 6/6 NYLON (94V-2) | 仕上 (FINISH) --- | 一般公差 (GENERAL TOLERANCE) 10以下: ±0.2 10以上-30以下: ±0.25 30以上-100以下: ±0.3 角 度: ±3° |
| DR. M. SUZUKI 17. JAN. '95 | DE. M. SUZUKI 17. JAN. '95 | LOC 番号 (No.) B J C-172076 |
| CHK. H. TAGUTCH 20. JAN. '95 | APP. H. TAGUTCH 20. JAN. '95 | 尺度 (SCALE) 4-1 |
| | | REV. H7 SHEET 1 OF 1 |

(CUSTOMER DRAWING) 参 考 区 面