




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50	F	REVISED PER ECR-13-004343	30JUL13	KH KR



- 1 FITS 0.51±0.025 X 4.75 [.020±.001 X .187] TAB
- 2 WIRE SIZE: 1.3-2.0mm<sup>2</sup> [16-14 AWG], STRANDED ONLY.  
 ONE WIRE STRIP LENGTH 7.94 [.312]  
 TWO WIRE STRIP LENGTH 8.51 [.335]
- 3 INSULATION SIZE: 6.60 [.260] MAX DIA.
- 4 CONTINUOUS STRIP.



TYPE 6/6 NYLON	BLUE TRANSLUCENT	BRASS	TIN	3-520997-2
MATERIAL	COLOR	MATERIAL	FINISH	PART NUMBER
HOUSING			TERMINAL	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	JR RUTH	7/23/92	 TE Connectivity RECEPTACLE, ASSEMBLY, FLAG, ULTRA-FAST, .187 SERIES
DIMENSIONS: mm [INCHES]		CHK	MS FEHER	7/23/92	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	D BRATINA	7/23/92	
0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [.010] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC	108-2043	NAME	
MATERIAL	SEE TABLE	FINISH	SEE TABLE	114-2123	SIZE
MATERIAL		FINISH		WEIGHT	CAGE CODE
SEE TABLE		SEE TABLE		-	A2 00779
CUSTOMER DRAWING				SCALE	DRAWING NO
CUSTOMER DRAWING				8:1	C=520997
CUSTOMER DRAWING				SHEET	RESTRICTED TO
CUSTOMER DRAWING				1 OF 1	-
CUSTOMER DRAWING				REV	F

520997