



注記
NOTE

- 1 ウエハーのそりは、長さ 25.4 に対して 0.24 MAX..
CAMBER MUST BE 0.24 MAX. PER 25.4
- △ 全極数が偶数の場合のみ適用。
TO BE APPLIED ONLY WHEN ALL CKTS. ARE EVEN.

44.64	40.64	▲ -109I	▲ -09A	9
34.48	30.48	-107I	-07A	7
29.4	25.4	-106I	-06A	6
24.32	20.32	-105I	-05A	5
19.24	15.24	▼ -104I	▼ -04A	4
14.16	10.16	▼ -103I	▼ -03A	3
9.08	5.08	10-32-102I	5281-02A	2
B	A	EDP NO.	ENG. NO.	極数 NO. OF CKTS.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS	SCALE	CURRENT REV DESC: REMOVED OBSOLETE PART NUMBER AS PER PCN#509989.		
mm	4:1			
GENERAL TOLERANCES (UNLESS SPECIFIED)				
	MM	INCH	EC NO: 708673 DRWN: SANTHN 2022/05/11 CHK'D: GGA 2022/06/22 APPR: GGA 2022/06/22	
4 PLACES	±	±	INITIAL REVISION:	
3 PLACES	±	±	DRWN: TYAJIMA01 2014/03/13	
2 PLACES	±	±	APPR: NUKITA 2014/03/13	
1 PLACE	±	±	DOCUMENT NUMBER	DOC TYPE
0 PLACES	±	±	SD-5281-001	PSD
ANGULAR TOL ± 1.0°		THIRD ANGLE PROJECTION	DRAWING	SERIES
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			A3-SIZE	5281
		MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
		SEE TABLE	GENERAL MARKET	1 OF 1

GENERAL TOLERANCES (UNLESS SPECIFIED)		
10 UNDER		±0.15
10 OVER	30 UNDER	---
30 OVER		---