


H	针长1.3mm
	针长1.6mm
	针长2.0mm



RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm


A

B

C

D

E



SPECIFICATION:

1. CURRENT RATING: 3.0A MAX
2. VOLTAGE: 150V AC/1mA MAX
3. TEMPERATURE RANGE: -55 °C ~ 85 °C
4. CONTACT RESISTANCE: 30 MEGOHMS MAX
5. INSULATION RESISTANCE: 100 MEGOHMS MIN.
6. INSERTION FORCE: 5N~20N
7. UNMATING FORCE: 8N~20N
8. DURABILITY: 10,000 CYCLES

A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND			VBUS	CC1	D+	D-	VBUS				GND
GND			VBUS		D-	D+	CC2	VBUS			GND
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1

序号	名称	用量	品名规格
1	外壳	1	Type:侧插14PIN 加高2.6外壳 SUS304 T=0.3mm
2	后盖	1	Type:侧插14PIN 后盖 SUS201 T=0.2mm
3	Molding 3	1	Type:侧插 Molding DIP 14PIN 黄铜 LCP黑色 加高2.6半成品
3.1	Molding 1	1	Molding DIP 14PIN Molding 上 黄铜 T=0.15 LCP黑色 加高2.6
3.2	Molding 2	1	Molding DIP 14PIN Molding 下 黄铜 T=0.15 LCP黑色 加高2.6
3.3	卡勾	1	Type:侧插 DIP 14PIN 卡勾 SUS301 T=0.15mm

G-Switch Electronic (HongKong) CO., Ltd.



品致科技
Unless otherwise specified, Tolerance:
X X.X
X.XX
X.XXX
Angles

DESIGN LI Qingqi	DATE 2022.06.10	Mold code:
CHECKED	DATE	GT-USB-7037A
APPROVED	DATE	
http://www.dg-switch.com		
REV.: X1	SCALE: 4:1	UNIT: mm
SIZE: A4	SHEET: 1/1	



5

4

3

2

1