



Specification

Operation (Torque)	200 ± 50GF
Operating Life	300,000
Contact rating	50mA@12V DC.
Insulation resistance	DC500V-1GΩ MIN
Contact resistance	100mΩ max. initial
Dielectric Strength	250 V AC (1mm)
Travel	0.25 ± 0.1mm
Waterproof grade	IP67

X: ±0.50	X°: ± 2°	UNITS	<p>THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED, OR TRANSMITTED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD</p>
X: ±0.30	X°: ± 1°	mm	
.XX ±0.10	.XX° ± 0.5°	MAT'L	
XXX ± 0.05		FINISH	
		Q'TY	
<p>yi yUAN 深圳市怡远科技有限公司 SHENZHEN YIYUAN TECHNOLOGY CO.,LTD</p>		PART NO.	
		YTS2282G	
APPD: RODGER	TITLE: TACTILE SWITCH		DWG NO: YTS2282G
CHKD: RDC			SCALE SHEET REV. 1/1
DR: BILLY WANG			REV. A1