



1. FIGURE AND DIMENSIONS(视图及尺寸)



X1511H-XX-N0

XXXXXT-PXX-AXXXX-LXXX-TX
 ① ② ③ ④ ⑤

- ① 系列 (Series No)
- ② 材质 (Material) :P-PSN(磷铜先镀锡后冲)
- ③ 线规线色 (Wire gauge line color) A:(AWG30-AWG24)
Circuit:R(red)/B (black) /Y (yellow) /G (green) /
 L (blue) /P (purple) /YR (orange) /W (white)
- ④ 线长 (Line length) L:(可定制长度)
- ⑤ 剥皮镀锡 (Peeled tin plated) T(可定制剥皮长度镀锡)

2. CIRCUIT DIAGRAM(接线图)

A	颜色	B
1	红色	
2	黑色	

3. MATERIAL(材料)

标志	料号	单用量	备注	总用量
1	X1511H-02-N0	1PCS		
2	X1511T-PSN	2PCS		
3	UL1007/24AWG. 红. 黑	各1PCS	200MM	
总量				

					ANGLAR	±5°	XKIB	DSND		SCALE: N/A	DRAWING NO. X1511T-PSN-A24RB-L200-T3		
					L ≤ 4	±0.2		DWN		VIEW:	PART NO.:		
					4 < L ≤ 16	±0.3		CHKD		UNIT: mm/in	DWG NO.:		
					16 < L ≤ 63	±0.4		APPD		SIZE: A4			
					L > 63	±0.5							
REVISIONS					UNSPECIFIED TOLERANCES			XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT	SHEET	REVISION
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn												1/1	A0