



# 1.FIGURE AND DIMENSIONS(视图及尺寸)



端面

X1511H-XX-N0

XXXXXT-PXX-AXXXXXX-LXXX-XXXXXT-X  
① ② ③ ④ ⑤ ⑥

- ① 系列 (Series No)
- ② 材质 (Material) :P-PSN(磷铜先冲后镀锡)
- ③ 线规线色 (Wire gauge line color) A:(AWG30-AWG24)  
Circuit:R(red)/B (black) /Y (yellow) /G (green) /  
L (blue) /P (purple) /YR (orange) /W (white)
- ④ 线长 (Line length) L:(可定制长度)
- ⑤ 系列 (Series No)
- ⑥ 正反接 (Positive and negative) Z(反接)/F (正接)

## 2. CIRCUIT DIAGRAM(接线图)

A	颜色	B
1	红色	2
2	黑色	1

## 3. MATERIAL(材料)

标志	料号	单用量	备注	总用量
1	X1511H-02-N0	2PCS		
2	X1511T-PSN	4PCS		
3	UL1007/28AWG. 红. 黑.	各1PCS	200MM	
总量				

REVISIONS					UNSPECIFIED TOLERANCES		XKIB	XKB INDUSTRIAL PRECISION CO.,LIMITED				
Δx					ANGULAR	±5°		DSND	SCALE: N/A	DRAWING NO.		
Δx					L ≤ 4	±0.2		DWN	VIEW:	X1511T-PSN-A28RB-L200-X1511T-F		
Δx					4 < L ≤ 16	±0.3		CHKD	UNIT: mm/in	PART NO.:		
MARK	DESCRIPTION	DATE	REVISED	APPROVED	16 < L ≤ 63	±0.4	APPD	SIZE: A4	DWG NO.:			
					L > 63	±0.5			WEIGHT	SHEET	REVISION	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn										1/1	A0	