



1. FIGURE AND DIMENSIONS (视图及尺寸)



XXXXXT-PXX-AXXXX-LXXX-TX
① ② ③ ④ ⑤

- ① 系列 (Series No)
- ② 材质 (Material) : P-PSN (磷铜先冲后镀锡)
- ③ 线规线色 (Wire gauge line color) A: (AWG26-AWG22)
Circuit: R (red) / B (black) / Y (yellow) / G (green) / L (blue) / P (purple) / YR (orange) / W (white)
- ④ 线长 (Line length) L: (可定制长度)
- ⑤ 剥皮镀锡 (Peeled tin plated) T (可定制剥皮长度镀锡)

2. CIRCUIT DIAGRAM (接线图)

A	颜色	B
Circuit1	红色	
Circuit2	黄色	
Circuit3	黄色	
Circuit4	黑色	

3. MATERIAL (材料)

标志	料号	单用量	备注	总用量
1	X2530H-04-N0	1PCS		
2	X2530TF-PSN	4PCS		
3	UL1007/22AWG. 红. 黑. 黄色	红黑各 1PCS 黄 2PCS	300MM	
总量				

DSND		SCALE: N/A	DRAWING NO. X2530T-PSN-A22RYB-L300-T3		
DWN		VIEW:	PART NO.:		
CHKD		UNIT: mm/in	DWG NO.:		
APPD		SIZE: A4	WEIGHT	SHEET	REVISION
XKB INDUSTRIAL PRECISION CO., LIMITED				1/1	A0

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
Δx					ANGULAR ±5°
Δx					L ≤ 4 ±0.2
Δx					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5

