




1.FIGURE AND DIMENSIONS(视图及尺寸)



X8821H-XX-N0

XXXXXT-PXX-AXXXXXX-LXXX-XXXXXT-X
 ① ② ③ ④ ⑤ ⑥

- ① 系列 (Series No)
- ② 材质 (Material) :P-BSN(磷铜先镀锡后冲)
- ③ 线规线色 (Wire gauge line color) A:(AWG26-AWG22)
 Circuit:R(red)/B (black) /Y (yellow) /G (green) /
 L (blue) /P (purple) /YR (orange) /W (white)
- ④ 线长 (Line length) L:(可定制长度)
- ⑤ 系列 (Series No)
- ⑥ 正反接 (Positive and negative) Z(反接)/F (正接)

2. CIRCUIT DIAGRAM(接线图)

| A | 颜色 | B |
|----------|-----|----------|
| Circuit1 | 红白色 | Circuit2 |
| Circuit2 | 红白色 | Circuit1 |
| | | |
| | | |
| | | |
| | | |

3. MATERIAL(材料)

| 标志 | 料号 | 单用量 | 备注 | 总用量 |
|----|-----------------------|-------------|-------|-----|
| 1 | X8821H-02-N0 | 2PCS | | |
| 2 | X8821T-PSN | 4PCS | | |
| 3 | UL2468/26AWG. 红白排线 | 红白排线 PCS | 300MM | |
| 总量 | | | | |

| MARK | DESCRIPTION | DATE | REVISED | APPROVED | UNSPECIFIED TOLERANCES |
|---|-------------|------|---------|----------|------------------------|
| Δx | | | | | ANGLAR ±5° |
| Δx | | | | | L ≤ 4 ±0.2 |
| Δx | | | | | 4 < L ≤ 16 ±0.3 |
| | | | | | 16 < L ≤ 63 ±0.4 |
| | | | | | L > 63 ±0.5 |
| REVISIONS | | | | | |
| www.helloxkb.com www.helloxkb.cn www.xk-dg.cn | | | | | |



| | | | |
|---------------------------------------|-------------|--|-------|
| DSND | SCALE: N/A | DRAWING NO. X8821T-PSN-A26 (RW) 2-L300-X8821T-F | |
| DWN | VIEW: | PART NO.: | |
| CHKD | UNIT: mm/in | DWG NO.: | |
| APPD | SIZE: A4 | WEIGHT | SHEET |
| | | 1/1 | |
| XKB INDUSTRIAL PRECISION CO., LIMITED | | REVISION | A0 |