




1. FIGURE AND DIMENSIONS (视图及尺寸)



XXXXXT-PXX-AXXXXXX-LXXX-XXXXXT-X
 ① ② ③ ④ ⑤ ⑥

- ① 系列 (Series No)
- ② 材质 (Material) :P-BSN(黄铜先冲后镀镀锡)
- ③ 线规线色 (Wire gauge line color) A:(AWG22-AWG18)
 Circuit:R(red)/B (black) /Y (yellow) /G (green) /
 L (blue) /P (purple) /YR (orange) /W (white)
- ④ 线长 (Line length) L:(可定制长度)
- ⑤ 系列 (Series No)
- ⑥ 正反接 (Positive and negative) Z(反接)/F (正接)

2. CIRCUIT DIAGRAM (接线图)

| A | 颜色 | B |
|----------|----|----------|
| Circuit1 | 红色 | Circuit5 |
| Circuit2 | 黄色 | Circuit4 |
| Circuit3 | 黄色 | Circuit3 |
| Circuit4 | 黄色 | Circuit2 |
| Circuit5 | 黑色 | Circuit1 |

3. MATERIAL (材料)

| 标志 | 料号 | 单用量 | 备注 | 总用量 |
|----|---------------------------|--------------------------|-------|-----|
| 1 | X9396H-05-N0 | 2PCS | | |
| 2 | X9396T-BSN | 10PCS | | |
| 3 | UL1007/20AWG. 红. 黑. 黄色 | 红黑各 1PCS 黄 3PCS | 300MM | |
| 总量 | | | | |

| | | | |
|---------------------------------------|-------------|--|--------------|
| DSND | SCALE: N/A | DRAWING NO. X9396T-PSN-A20RYYYB-L300-X9396T-F | |
| DWN | VIEW: | PART NO.: | |
| CHKD | UNIT: mm/in | DWG NO.: | |
| APPD | SIZE: A4 | WEIGHT | SHEET 1/1 |
| XKB INDUSTRIAL PRECISION CO., LIMITED | | REVISION | A0 |

| | | | | | | |
|------------------------|-------------|------|---------|----------|-------------|------|
| Δx | | | | | ANGULAR | ±5° |
| Δx | | | | | L ≤ 4 | ±0.2 |
| Δx | | | | | 4 < L ≤ 16 | ±0.3 |
| MARK | DESCRIPTION | DATE | REVISED | APPROVED | 16 < L ≤ 63 | ±0.4 |
| REVISIONS | | | | | L > 63 | ±0.5 |
| UNSPECIFIED TOLERANCES | | | | | | |

