



1. FIGURE AND DIMENSIONS (视图及尺寸)

RU
E523734

RU
E523734



X9821HM-XXA-N0HF

XXXXXT-PXX-AXXXXXX-LXXX-XXXXXT-X

① ② ③ ④ ⑤ ⑥

- ① 系列 (Series No)
- ② 材质 (Material) :P-PSN(磷铜先冲后镀锡)
- ③ 线规线色 (Wire gauge line color) A:(AWG32-AWG28)
Circuit: R(red)/B (black) /Y (yellow) /G (green) /
L (blue) /P (purple) /YR (orange) /W (white)
- ④ 线长 (Line length) L:(可定制长度)
- ⑤ 系列 (Series No)
- ⑥ 正反接 (Positive and negative) Z(反接)/F (正接)

2. CIRCUIT DIAGRAM (接线图)

| A | 颜色 | B |
|---|----|---|
| 1 | 红色 | 1 |
| 2 | 黑色 | 2 |
| 3 | 绿色 | 3 |
| 4 | 黄色 | 4 |

3. MATERIAL (材料)

| 标志 | 料号 | 单用量 | 备注 | 总用量 |
|----|------------------------------|-------|-------|-----|
| 1 | X9821HM-04A-N0HF | 2PCS | | |
| 2 | X9821TF-PSN | 8PCS | | |
| 3 | UL1007/28AWG. 红. 黑. 绿. 黄色 | 各1PCS | 300MM | |
| 总量 | | | | |

| MARK | DESCRIPTION | DATE | REVISED | APPROVED | UNSPECIFIED TOLERANCES |
|---|-------------|------|---------|----------|------------------------|
| Δx | | | | | ANGULAR ±5° |
| Δx | | | | | L ≤ 4 ±0.2 |
| Δx | | | | | 4 < L ≤ 16 ±0.3 |
| | | | | | 16 < L ≤ 63 ±0.4 |
| | | | | | L > 63 ±0.5 |
| REVISIONS | | | | | |
| www.helloxkb.com www.helloxkb.cn www.xk-dg.cn | | | | | |

XKIB

| DSND | SCALE: N/A | DRAWING NO. |
|--|-------------|----------------------------------|
| DWN | VIEW: | X9821T-PSN-A28RBYG-L300-X9821T-Z |
| CHKD | UNIT: mm/in | PART NO.: |
| APPD | SIZE: A4 | DWG NO.: |
| XKIB INDUSTRIAL PRECISION CO., LIMITED | | WEIGHT |
| | | SHEET 1/1 |
| | | REVISION A0 |