





Specifications:
规格:

Voltage rating: 50V AC/DC
额定电压: 50V AC/DC
Current rating: 0.5A AC/DC
额定电流: 0.5A AC/DC
Withstanding voltage: 250V AC/minute
耐受电压: 250V AC/分钟
Temperature range: -40°C~+105°C
温度范围: -40°C~+105°C
Insulation resistance: 500MΩ
绝缘电阻: 500MΩ
Contact resistance: 100mΩ
接触电阻: 100mΩ

X0815 F V S - XX A S - 9T V01
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- Series No
- Category: Female
- Welding Board Angle: V-Stright 180°
- Welding Way: S-SMT
- Row No. Pin No: XX-10-100Pin
- Category: A-8.45mm Height
- Special No: S-With positioning column
- Material: 9T-PA9T UL94V-0
CAP Material: PA6T UL94V-0
- Plating: Gold Plated 4u" MIN



WITH CAP

Recommended PCB Layout
General Tolerance: ±0.05

X0815FVS-XXAS-9TV01	X0815WRS-XXAS-9TV01	/
	X0815WVS-XXBS-9TV01	11.75mm±0.5
	X0815WVS-XXCS-9TV01	24.7mm±0.5
	X0815WVS-XXDS-9TV01	9.75mm±0.5
	X0815WVS-XXES-9TV01	12.75mm±0.5
	X0815WVS-XXFS-9TV01	19.5mm±0.5
PART NO		Suitable XKB Wafer
		Mating Height

Poles	Dimensions(mm)						
	A	B	C	D	E	F	G
10	6.55	4.90	3.20	12.82	7.80	10.00	13.00
20	10.55	8.90	7.20	16.82	11.80	14.00	17.00
30	14.55	12.90	11.20	20.82	15.80	18.00	21.00
40	18.55	16.90	15.20	24.82	19.80	22.00	25.00
50	22.55	20.90	19.20	28.82	23.80	26.00	29.00
60	26.55	24.90	23.20	32.82	27.80	30.00	33.00
70	30.55	28.90	27.20	36.82	31.80	34.00	37.00
80	34.55	32.90	31.20	40.82	35.80	38.00	41.00
90	38.55	36.90	35.20	44.82	39.80	42.00	45.00
100	42.55	40.90	39.20	48.82	43.80	46.00	49.00

X0815FVS-XXAS-9TV01	PA9T	Phosphor Bronze	X0815W
PART NO	Material	Material(Pin)	Suitable XKB Wafer

DSND	SCALE: N/A	MODEL TYPE: 0.8mm BTB Connector
DWN	VIEW:	PART NO.: X0815FVS-XXAS-9TV01
CHKD	UNIT: mm/in	DWG NO.:
APPD	SIZE: A4	X-X0815FVS-XXAS-9TV01
		WEIGHT
		SHEET
		REVISION



XKB INDUSTRIAL PRECISION CO., LIMITED

广东星坤科技股份有限公司

Δx	日期
Δx	日期
Δx	日期

文件工程章

MARK	DESCRIPTION	DATE	REVISED	APPROVED	ANGLAR	±5°
					L ≤ 4	±0.2
					4 < L ≤ 16	±0.3
					16 < L ≤ 63	±0.4
					L > 63	±0.5
UNSPECIFIED TOLERANCES						

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn