





WITH CAP



WITH CAP



Recommended PCB Layout

Specifications:

规格:

- Voltage rating: 50V AC/DC
- 额定电压: 50V AC/DC
- Current rating: 0.5A AC/DC
- 额定电流: 0.5A AC/DC
- Withstanding voltage: 250V AC/minute
- 耐受电压: 250V AC/分钟
- Temperature range: -40°C~+105°C
- 温度范围: -40°C~+105°C
- Insulation resistance: 500MΩ
- 绝缘电阻: 500MΩ
- Contact resistance: 100mΩ
- 接触电阻: 100mΩ

X0815 W V S - XX E S - 9T V01
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- Series No
- Category: W-Wafer
- Welding Board Angle: V-Stright 180°
- Welding Way: S-SMT
- Row No. Pin No: XX-30-80Pin
- Category: E-7.8mm Height
- Special No: S-With positioning column
- Material: 9T-PA9T UL94V-0
CAP: PA6T UL94V-0
- Plating: Gold Plated 4u" MIN

Poles	Dimensions(mm)				
	A	B	C	D	E
30	11.20	13.00	14.40	16.30	16.10
40	15.20	17.00	18.40	20.30	20.10
50	19.20	21.00	22.40	24.30	24.10
60	23.20	25.00	26.40	28.30	28.10
70	27.20	29.00	30.40	32.30	32.10
80	31.20	33.00	34.40	36.30	36.10

X0815WVS-XXES-9TV01	PA9T	Phosphor Bronze	X0815FVS-A	12.75mm±0.5
			X0815FVS-B	9.0mm±0.5
PART NO	Material	Material(Pin)	Suitable XKB Wafer	Mating Height

DSND		SCALE: N/A	MODEL TYPE: 0.8mm BTB Connector
DWN		VIEW:	PART NO.: X0815WVS-XXES-9TV01
CHKD		UNIT: mm/in	DWG NO.: X-X0815WVS-XXES-9TV01
APPD		SIZE: A4	WEIGHT
XKB INDUSTRIAL PRECISION CO., LIMITED			SHEET
			REVISION
			1/1
			A0

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	



广东星坤科技股份有限公司

文件工程章

MARK	DESCRIPTION	DATE	REVISED	APPROVED
REVISIONS				
www.helloxkb.com	www.helloxkb.cn www.xk-dg.cn			