



Specifications:



规格:
Voltage rating:50V AC/DC
 额定电压: 50V AC/DC
Current rating:0.5A AC/DC
 额定电流: 0.5A AC/DC
Withstanding voltage:250V AC/minute
 耐受电压: 250V AC/分钟
Temperature range:-40°C~+105°C
 温度范围: -40°C~+105°C
Insulation resistance:500MΩ
 绝缘电阻: 500MΩ
Contact resistance:100mΩ
 接触电阻: 100mΩ



X0815 F V S - XX A S - 9T V01

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

1. Series No
2. Category:Female
3. Welding Board Angle:V-Stright 180°
4. Welding Way:S-SMT
5. Row No.Pin No:XX-10-100Pin
6. Category:A-8.45mm Height
7. Special No:S-With positioning column
8. Material:9T-PA9T UL94V-0
CAP Material: PA6T UL94V-0
9. Plating:Gold Plated 4u" MIN



WITH CAP

| | | |
|---------------------|---------------------|---------------|
| X0815FVS-XXAS-9TV01 | X0815WRS-XXAS-9TV01 | / |
| | X0815WVS-XXBS-9TV01 | 11.75mm±0.5 |
| | X0815WVS-XXCS-9TV01 | 24.7mm±0.5 |
| | X0815WVS-XXDS-9TV01 | 9.75mm±0.5 |
| | X0815WVS-XXES-9TV01 | 12.75mm±0.5 |
| | X0815WVS-XXFS-9TV01 | 19.5mm±0.5 |
| X0815WVS-XXGS-9TV01 | 18.0mm±0.5 | |
| PART NO | Suitable XKB Wafer | Mating Height |

| Poles | Dimensions(mm) | | | | | | |
|-------|----------------|-------|-------|-------|-------|-------|-------|
| | A | B | C | D | E | F | G |
| 10 | 6.55 | 4.90 | 3.20 | 12.82 | 7.80 | 10.00 | 13.00 |
| 20 | 10.55 | 8.90 | 7.20 | 16.82 | 11.80 | 14.00 | 17.00 |
| 30 | 14.55 | 12.90 | 11.20 | 20.82 | 15.80 | 18.00 | 21.00 |
| 40 | 18.55 | 16.90 | 15.20 | 24.82 | 19.80 | 22.00 | 25.00 |
| 50 | 22.55 | 20.90 | 19.20 | 28.82 | 23.80 | 26.00 | 29.00 |
| 60 | 26.55 | 24.90 | 23.20 | 32.82 | 27.80 | 30.00 | 33.00 |
| 70 | 30.55 | 28.90 | 27.20 | 36.82 | 31.80 | 34.00 | 37.00 |
| 80 | 34.55 | 32.90 | 31.20 | 40.82 | 35.80 | 38.00 | 41.00 |
| 90 | 38.55 | 36.90 | 35.20 | 44.82 | 39.80 | 42.00 | 45.00 |
| 100 | 42.55 | 40.90 | 39.20 | 48.82 | 43.80 | 46.00 | 49.00 |

Recommended PCB Layout
 General Tolerance:±0.05

| | | | |
|---------------------|----------|-----------------|--------------------|
| X0815FVS-XXAS-9TV01 | PA9T | Phosphor Bronze | X0815W |
| PART NO | Material | Material(Pin) | Suitable XKB Wafer |

| | | |
|------|-------------|------------------------------------|
| DSND | SCALE: N/A | MODEL TYPE: 0.8mm BTB Connector |
| DWN | VIEW: | PART NO.: X0815FVS-XXAS-9TV01 |
| CHKD | UNIT: mm/in | DWG NO.: |
| APPD | SIZE: A4 | X-X0815FVS-XXAS-9TV01 |
| | | WEIGHT |
| | | SHEET |
| | | REVISION |



XKB INDUSTRIAL PRECISION CO.,LIMITED

广东星坤科技股份有限公司

| MARK | DESCRIPTION | DATE | REVISED | APPROVED | UNSPECIFIED TOLERANCES |
|------|-------------|------|---------|----------|------------------------|
| Δx | | | | | ANGULAR ±5° |
| Δx | | | | | L ≤ 4 ±0.2 |
| Δx | | | | | 4 < L ≤ 16 ±0.3 |
| | | | | | 16 < L ≤ 63 ±0.4 |
| | | | | | L > 63 ±0.5 |

文件工程章

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

1/1
AO