




- NOTES:**
- *Material
 - Body: LCP Rated: Color: Black.
 - Shield: Brass
 - plating: Nickel Plating.
 - Contact: Phosphor Bronze.
 - plating: Gold plating Over Nickel on contact Area; Tin plating on solder tail
 - *Electrical Specification
 - Operation Voltage: 40 VAC max
 - Current Rating: 0.5 Ampere per contact
 - Contact Resistance: 30 Milliohms max.
 - Insulation Resistance: 2000 Megohms min.
 - Dielectric Withstanding Voltage: 500VAC
 - *Environmental
 - Operating Temperature: -20C to +85C
 - *How TO Order

深圳市金航标电子有限公司	www.kinghelm.com.cn	HD-0013							 	P/No:	
		Customer:	Approval	Check	Drawn	Unit	Scale	Date			
KH-HDMI-0013	0755-28190160	Drawing No:			ba bm	mm			Singna luer		