




REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
01	NEW	INITIAL RELEASE.	09-13-04	XIAO PING
02	△	變更料號	2008.10.07	彭思城
03	△	變更圖號	2012.04.02	黃小燕



Specifications  
 Current Rating: 2Amp  
 Insulation Resistance: 1000MΩMin.  
 Dielectric Withstanding Voltage: 500VAC  
 Contact Resistance: 20mΩMax.  
 Operating Temperature: -40°C to +105°C  
 Materials  
 Contact Material: Brass  
 Insulator Material: Thermoplastic, UL 94V-0 PBT or the equivalent material  
 All materials must meet Greenconn requirement for environment protection.


### Ordering Information

G PFA201 - XX XX A 001 A 1 B X

No. of Pins per Row 02~40  
 Standard Plating 02=Gold Flash  
 Selective Plating 01=Tin  
 05=Gold Flash/Tin

Color 1=Black  
 Standard Packing A=box  
 Selective Packing C=Tube

Recommended P.C.Board Layout  
 (Tolerance: ±0.05)



格稜股份有限公司  
**Greenconn Corporation**

GENERAL TOLERANCE		DESIGN: 黃小燕	DATE: 2012.04.02
X.*±5.0°	X.±0.30	CHECKED: 劉北平	DATE: 2012.04.02
.X*±3.0°	.X±0.25	AUDITED: 李輝	DATE: 2012.04.02
.XX*±2.0°	.XX±0.15	APPROVED: cc_li	DATE: 2012.04.02
.XXX*±1.0°	.XXX±0.10		

DWG. NO.	△ △ GPFA201-CA1AB
PART NO.	△ GPFA201-XXXX A001A1BX

TITLE:  
 2.00 PIN HEADER  
 DUAL ROWS DIP TYPE  
 CONNECTOR

F  
E  
D  
C  
B  
A

F  
E  
D  
C  
B  
A

1 2 3 4 5 6 7 8 9

1 2 3 4 5 6 7 8 9