



REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
03	△	變更料號	2008.10.29	彭思城
04	△	依上級要求變更圖號	2011.01.04	李芳忠



Specifications
 Current Rating: 2Amp
 Insulation Resistance: 1000MΩMin.
 Dielectric Withstanding Voltage: 500VAC
 Contact Resistance: 20mΩMax.
 Operating Temperature: -40°C to +105°C
 Materials
 Contact Material: Brass
 Insulator Material: Thermoplastic, UL 94V-0 PBT or the equivalent material
 All materials must meet Greenconn requirement for environment protection.

Ordering Information

G PFB101 - XX XX A 001 A 1 B X


No. of Pins per Row
 △ 02~40

Standard Plating
 02=Gold Flash
 Selective Plating
 01=Tin
 05=Gold Flash/Tin

Color
 1=Black

Standard Packing
 A=Box
 Selective Packing
 C=Tube

Recommended P.C.Board Layout
 (Tolerance: ±0.05)



格稜股份有限公司
Greenconn Corporation

GENERAL TOLERANCE	
X.*±5.0°	X.±0.30
.X*±3.0°	.X±0.25
.XX*±2.0°	.XX±0.15
.XXX*±1.0°	.XXX±0.10

DESIGN: 李芳忠	DATE: 2011.01.04
CHECKED: 劉北平	DATE: 2011.01.04
AUDITED: 李輝	DATE: 2011.01.04
APPROVED: cc_li	DATE: 2011.01.04

DWG. NO.	△ △
	GPFB101-CA1AB
PART NO.	△
	GPFB101-XXXX A001A1BX

TITLE:
 2.00 PIN HEADER
 SINGLE ROW R/A TYPE
 CONNECTOR

REV.	UNIT.	SCALE.	PAGE.	
04	mm	5:1	1/1	