



PCB Layout(Pattern side)



Circuit Diagram



NO.1	
PART NO	H
A	3.8
B	4.3
H	4.5
C	4.8
D	5.0
J	5.5
E	6.0
K	6.5
F	7.0
L	7.5
G	8.0

NO.2-NO.3	
PART NO	NOTE
01~99	SERIAL NUMBER

Typical Specifications

- 1.Rating : DC 12V 50mA
- 2.Contact Resistance: $\leq 50m\Omega$
- 3.Insulation Resistance: $\geq 100m\Omega$
- 4.Operating Force: $250\pm 40gf$
- 5.Travel: $0.25\pm 0.1mm$
- 6.Life : 100,000 Cycles

⑤	Cover	—	1	SPCC	Tin Plated	—
④	Keystoke	—	1	PPA	Black	—
③	Contact	—	1	F.Ag/SUS	Plating silver	—
②	Base	—	1	PPA	Black	—
①	Terminal	—	2	Brass(0.3t)	Plating silver	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE		 ELECTRONICS CO.,LTD						
DRAWN	LIUCAN	2021.9.24								
CHECKED				TITLE: TACT SWITCHES						
APPROVALS				PART NO. K2-1109AP-□4SW-□□						
TOLERANCES ARE			30~以上	±0.30	ANGLE	UNIT: mm				
			10~30	±0.20						
			5~10	±0.15						
			~ 5	±0.10	±2'	DRAWING NO.				
							SCALE: 1:1	PROJ:		
ECN NO.	REV.	DATE.	NEW DESCRIPTION.			CHANGE.	CHECK.	APPRO.	DRAWING NO.	SHEET 1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
—	A	—	NEW DESCRIPTION.	—	—	—