





A B C D E F



N=PIN数

Material 材料
 Insulator 塑胶: PBT (UL 94V-0)
 Contact 端子: Brass 黄铜
 Surface Coating 表面镀层: Gold Over Nickel 里镍外金
 Electrical Characteristics 电气特性
 Current rating 额定电流: 2.5Amps
 Dielectric Withstanding Voltage 耐压:
 AC 500V for 1 Minute.
 Insulator Resistance 绝缘电阻: 1000MΩ Min.
 Contact Resistance 接触电阻: 20mΩ Max.
 Operating Temperature 工作温度: -40°C ~ +105°C
 Max. Processing Temp 瞬时温度:
 PBT 240° C for 6 seconds
 PA9T (260° C for 10 seconds)



P.C.B LAYOUT

未注尺寸公差			PZ2.54-1*N-fwz		上海洲日电子有限公司		
尺寸	公差				Shanghai Zhouri Electronics CO.,LTD		
	长度	角度	上海康司玛电子设备进出口有限公司 Shanghai KangSiMa Electronic Equipment import and export Co.,LTD			TEL:86-21-34975176/51571121	
X.	±0.3	±5°					
X.X	±0.2	±3°					
X.XX	±0.15						
制图	周元金	201171018	版本编号	20171018 A/1			
审核	张海娜	201171018	图纸编号	ZR20171018-258-1			
核准	章妹	201171018	物料编号				
			第三视角				
					1:1	mm	A4

A B C D E F