



SPECIFICATIONS:

Current Rating: 10A AC,DC
 Voltage Rating: 250V AC,DC
 Temperature Range: -40°C ~ +105°C
 Contact Resistance: 10mΩ Max
 Insulation Resistance: 1000MΩ Min
 Withstanding Voltage: 1500V AC/minute
 Material: Nylon 66,UL94V-0 (White)



CHANGJIANG CONNECTORS CO.,LTD.

Unit	Scale	Sheet
mm	4:1	1 of 1
Draw BY:	Approved :	
LIZQ	GONGYB	

Title :
7.92mm PITCH
HOUSING

General Tolerance	
x.x±0.25	ANGLE±
x.xx±0.20	
x.xxx±0.15	

DRAW NO : **A7921H-2P** REV **A0**

A0	NEW RELEEASE	2009.05.10
REV	DESCRIPTION	DATE